





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer drawing



Recommended PCB Layout
Tolerance: $\pm 0.05\text{mm}$

Dimensions

Positions	A	B	C	E
9	30.81	24.99	16.92	11.08
15	39.20	33.30	25.25	19.39
25	53.05	47.04	38.96	33.24
37	69.40	63.50	55.42	49.86

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	03/06/14	IP

D-SUB TECHNICAL DATA

SHELL: Steel, 100u" Tin Over 50u" min nickel over 50u" min Copper
BODY: PBT UL 94V-0
CONTACTS: Copper alloy,
Gold flash over 50u" min nickel on contact area.
100u" min tin over 50u" min nickel on solder area.
CLINCH NUT: Brass, 80u" min Nickel Plated
ELECTRICAL: Voltage rating 250 V Rms
Current Rating :3 AMP
Withstanding Voltage >1000 V Rms
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max
MARKING: Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717 TS X H XX P OL2

L: RoHS Compliance

Tinned shell
+dimples for plug

Straight PCB Termination
One Metal Shell
Connector

Shell Size:
E,A,B,C

Termination:
OL2 :L=6.02mm(.237")

Contact Type:
P=Pin

Configuration:
09,15,25,37

Mounting Options:
H=4-40

UNLESS OTHERWISE SPECIFIED
TOLERANCES

	U.S.	METRIC
.X	+/-	0.50
.XX	+/-	0.30
.XXX	+/-	0.20
FRACTIONS	+/-	5°
ANGLES	+/-	

FOR MATERIALS AND FINISHES
SEE NOTES

REMOVE SHARP EDGES


DIMENSIONS

U.S.	INCHES
METRIC	MM

APPROVAL	DATE
DRAWN Felix Liu	03/06/14
CHECKED Tony Tang	03/06/14
CHECKED	

DRAWING FILE :

ANGLE OF PROJECTION



Amphenol

Amphenol East Asia Limited A

TITLE

D-SUB connector,TS series

SIZE DRAWING NO.

A4 C L717TSXHXXPOL2

REV.

1

SCALE NONE

SHEET 1 OF 1