



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECO-13-009543 ADD P/N	28JUN13	CZ	WY
	D2	ECO-15-012967	09SEP15	JS	WY
	D3	ECR-19-000800	21JAN19	J.Y	E.J
	D4	ECR-19-004068	14MAR19	J.Y	E.J




A detailed line drawing of a ball joint assembly. The assembly consists of a lower control arm with a ball joint at its end, and a steering knuckle with a ball joint at its end. The two ball joints are shown connected to a central hub. Four numbered callouts point to specific parts: 1 points to the upper ball joint, 2 points to the lower ball joint, 3 points to the hub, and 4 points to the lower control arm.

ISOMETRIC FOR -1/-3/-5



ISOMETRIC FOR -6




DIRECTION OFF TOP OF REEL
ACC. TO TE SPEC. 107-3





-  DIMS FOR PART 2050216-6

	I			NUT M4			4
		I		NUT M4			3
I			I	NUT M4			2
I	I	I	I	TERMINAL	PHOS. BRONZE	PRE-TIN	I
6	-5	-3	-I	DESCRIPTION	MATERIAL	FINISH	ITEM
REQ. PRE ASSY							
2050216							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. ZHU	02NOV09	TE Connectivity		
		CHK W. YUAN	13NOV09			
DIMENSIONS:		APVD K. ODA	13NOV09	NAME		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3	PRODUCT SPEC		ASSY., TERMINAL_RING-TONGUE, M4		
	0 PLC 1			- SIZECAGE CODEDRAWING NO A200779C-2050216		
	1 PLC 10.1					
	2 PLC 10.01					
	3 PLC 10.001					
	4 PLC 10.0001					
ANGLES ±3°	APPLICATION SPEC	RESTRICTED TO				
FINISH	WEIGHT					
MATERIAL						
material 2		CUSTOMER DRAWING		SCALE 2:1	SHEET 1 of 2	REV D4

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. ZHU CHK W. YUAN APVD K. ODA	02NOV09 13NOV09 13NOV09	TE TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3		NAME ASSY., TERMINAL_RING_TONGUE, M4	
0-PLC 1-PLC 2-PLC 3-PLC 4-PLC ANGLES FINISH		±0.1 ±0.01 ±0.001 ±0.0001 ±3° -		SIZE A260779	
material_2		finish_spec_2		DRAWING NO C-2050216	
CUSTOMER DRAWING		SCALE 2:1		SHEET 2 OF 2	
				REV D4	