







| PART NUMBER | DIMENSION L |
|-------------|-------------|
| 203263-0006 | 26.0        |
| 203263-0016 | 20.0        |
| 203263-0026 | 14.0        |
| 203263-0036 | 36.0        |



DETAIL B  
SCALE 20:1

- NOTES:
- MATERIAL:  
BASE METAL: HIGH CONDUCTIVE COPPER ALLOY  
PLATING ON BODY: 3.18 MICRON MIN SILVER OVER 1.27 MICRON MIN NICKEL
  - PRODUCT SPECIFICATION: 2043130006-PS
  - APPLICATION SPECIFICATION: 2043130006-AS
  - PACKAGING SPECIFICATION: 2032630006-PK
  - SILVER COMPONENTS WILL BE SUPPLIED TARNISH FREE BUT MAY TARNISH OVER TIME.
  - MINIMUM RECOMMENDED BUSBAR THICKNESS IS 1.5MM



SECTION A-A

|                                                                                                                                                                                       |  |        |  |                                           |  |         |                  |           |          |                 |  |          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------|--|-------------------------------------------|--|---------|------------------|-----------|----------|-----------------|--|----------|
| THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION                                         |  |        |  |                                           |  |         |                  |           |          |                 |  |          |
| DIMENSION UNITS                                                                                                                                                                       |  | SCALE  |  | CURRENT REV DESC: PLATING SPEC<br>UPDATED |  |         | <div>molex</div> |           |          |                 |  |          |
| mm                                                                                                                                                                                    |  | 10:1   |  |                                           |  |         |                  |           |          |                 |  |          |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                                                                                                              |  |        |  | 6.0MM CST STD (PRESS FIT), MALE PIN       |  |         |                  |           |          |                 |  |          |
| ANGULAR TOL ± 0.5°                                                                                                                                                                    |  |        |  |                                           |  |         |                  |           |          |                 |  |          |
| 4 PLACES                                                                                                                                                                              |  | ±      |  |                                           |  |         |                  |           |          |                 |  |          |
| 3 PLACES                                                                                                                                                                              |  | ±      |  |                                           |  |         |                  |           |          |                 |  |          |
| 2 PLACES                                                                                                                                                                              |  | ± 0.15 |  | PRODUCT CUSTOMER DRAWING                  |  |         |                  |           |          |                 |  |          |
| 1 PLACE                                                                                                                                                                               |  | ± 0.25 |  |                                           |  |         |                  |           |          |                 |  |          |
| 0 PLACES                                                                                                                                                                              |  | ±      |  | DOCUMENT NUMBER                           |  |         | DOC TYPE         |           | DOC PART | REVISION        |  |          |
| DRAFT WHERE APPLICABLE<br>MUST REMAIN<br>WITHIN DIMENSIONS                                                                                                                            |  |        |  | 2032630006-SD                             |  |         | PSD              |           | 000      | C               |  |          |
|                                                                                                                                                                                       |  |        |  | THIRD ANGLE PROJECTION                    |  | DRAWING |                  | SERIES    |          | MATERIAL NUMBER |  | CUSTOMER |
| <div></div> |  |        |  | D-SIZE                                    |  | 203263  |                  | SEE TABLE |          | GENERAL MARKET  |  | 1 OF 1   |