
















REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A2		REVISE PER ECR-18-003981	03MAR2018	MB	GM
A3		REVISE PER ECO-18-007692	16MAY2018	JMS	GM
A4		REVISE PER ECO-18-012171	01AUG2018	JMS	GM
A5		REVISED PER ECO-19-008061	24MAY2019	JMS	GK

- NOTES:
- MATERIAL:
INNER HOUSING-NYLON 6/6,35% GLASS FILLED,BLACK
OUTER HOUSING-NYLON 6/6,35% GLASS FILLED,BLACK
PERIMETER SEAL-SILICONE RUBBER,INHERENTLY LUBRICATED,GREEN
GROMMET SEAL-SILICONE RUBBER,INHERENTLY LUBRICATED,BLUE
ISL-NYLON 6/6,35% GLASS FILLED,GRAY
CPA-PBT,30% GLASS FILLED,RED
LEVER-NYLON 6/6,35% GLASS FILLED,GRAY
 - 2203973-1 SHOWN IN GENERAL VIEWS.
 - ISL SHOWN IN PRE-SET, SHIPPING POSITION.
 - CPA SHOWN IN PRE-SET, SHIPPING POSITION.
 - TE PART NO. AND JULIAN DATE CODE (YY-DDD) MARKED IN APPROXIMATE LOCATION.
 - APPLICABLE TERMINALS: MCON 1.2 CLEAN BODY
TE P/N 1670144-X (0.5-0.75 SQ.MM.) ALL CIRCUITS
TE P/N 1452503-X (1.0-1.5 SQ.MM.) CIRCUITS 10 AND 17 ONLY.
 - MATES WITH TE HEADER ASSEMBLY: 2297721-X
 - SEE SHEET 2 FOR PART NUMBER TABLE WITH KEYING AND CIRCUIT CONFIGURATION OPTIONS.
 - PRELIMINARY DESIGN - NOT TOOLED.
 - APPLICABLE CAVITY PLUGS FOR UNUSED CIRCUITS:
TE P/N 1-1452424-2 (FOR CIRCUITS 10 & 17 ONLY)
TE P/N 1-1452424-1 (FOR ALL CIRCUITS EXCEPT 10 & 17)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: CHETHAN.K 13NOV2013	TE TE Connectivity	
		CHK: A.VASBINDER 15NOV2013		
		APVD: A.VASBINDER 15NOV2013		
		PRODUCT SPEC		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME: 26P SEALED MCON FEMALE ASSEMBLY	
mm		0 PLC ±0.5	SIZE: A1	
		1 PLC ±0.3	CAGE CODE: -	
		2 PLC ±0.3	DRAWING NO: C=2203973	
		3 PLC ±0.3	RESTRICTED TO: -	
		4 PLC ±0.3	SCALE: 2:1	
		ANGLES ±°	SHEET: 1 OF 2	
MATERIAL:		FINISH	REV: A5	
		WEIGHT: -		
		CUSTOMER DRAWING		

FORD	C727	EU5T-14A464-MAA-009	C10	A	1-2203973-3
FORD	C727	EU5T-14A464-MAA-008	C9	A	1-2203973-2
FORD	C1YB01F-A	EU5T-14A464-MAA-007	C8	A	1-2203973-1
FORD	V611/625	EU5T-14A464-MAA-006	C7	A	1-2203973-0
FORD	C482	EU5T-14A464-MAA-005	C6	A	2203973-9
FORD	CD6	EU5T-14A464-MAA-004	C5	A	2203973-8
FORD	CABLE SHIFT / STOP-START	EU5T-14A464-MAA-003	C4	A	2203973-7
FORD	SHIFT BY WIRE / NON STOP-START	EU5T-14A464-MAA-002	C3	A	2203973-6
FORD	CABLE SHIFT / NON STOP-START	EU5T-14A464-MAA-001	C2	A	2203973-5
VARIOUS	SHIFT BY WIRE / STOP-START VARIOUS (ALL OPEN)	VARIOUS	C1	D	2203973-4
			C1	C	2203973-3
			C1	B	2203973-2
			C1	A	2203973-1
OEM	APPLICATION	CUSTOMER PART NUMBER	CIRCUIT CONFIGURATION	KEYING CONFIGURATION	PART NUMBER



BLOCKED	2, 4, 7, 10, 11, 12, 13, 14, 17, 18, 20, 23	A	1-2203973-3
	4, 7, 10, 11, 12, 13, 14, 17, 18, 20, 23	A	1-2203973-2
	4, 7, 10, 11, 12, 13, 17, 18, 21, 22, 23	A	1-2203973-1
	4, 7, 10, 11, 12, 13, 14, 17, 20, 21, 22, 23	A	1-2203973-0
	4, 7, 10, 11, 12, 13, 17, 21, 22, 23	A	2203973-9
	7, 8, 9, 10, 11, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26	A	2203973-8
	26	A	2203973-7
	10, 17, 18, 19	A	2203973-6
	10, 12, 17, 18, 19, 26	A	2203973-5
	ALL OPEN	D	2203973-4
	ALL OPEN	C	2203973-3
	ALL OPEN	B	2203973-2
	ALL OPEN	A	2203973-1
CIRCUIT CONFIGURATION		KEYING CONFIGURATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: CHETHAN.K

CHK: A.VASBINDER

APVD: A.VASBINDER

13NOV2013

15NOV2013

15NOV2013

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±°

1 PLC ±0.5

2 PLC ±0.3

3 PLC ±°

4 PLC ±°

ANGLES ±°

FINISH

PRODUCT SPEC

APPLICATION SPEC

408-32149

WEIGHT

CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

-

©=2203973

SCALE

2:1

SHEET

2

OF

2

REV

A5

TE Connectivity

NAME

26P SEALED MCON FEMALE ASSEMBLY