




Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



Dichtfläche eben und gratfrei, geeignete Schraubenabdichtung ist vorzusehen / Sealing area must be flat and polished. provide suitable sealing for the screws

Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14	
Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	
Contact arrangement	IEC 60130-9 ¹⁾			-			-			-		
Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		
Rated voltage	UL 1977	250 V									60 V	
Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (840 V)			1200 V (500 V)	1500 V (840 V)		1200 V (500 V)				
Pollution degree ²⁾	IEC 60664-1	1 (3 ³⁾)										
Installation category	IEC 60664-1	I										
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600										
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C/+104°F		7A/+40°C/+104°F						3A/+40°C/+104°F		
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ⁴⁾										
Contact resistance	IEC 60512-2-1	<5m Ohm										
Climatic category	IEC 60668-1	40 / 100 / 56										
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F										
salt spray resistance	DIN IEC 60068-2-11	720h										
IP degree	IEC 60529	IP 69K / IP 67 / IP 65 (in mated condition)										
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N		50N	55N		60N	50N		
Mechanical operation	IEC 60512-9-1	silver ≥500 mating cycles gold ≥1000 mating cycles										
Housing material		brass and / or zinc die cast, nickel plated										
Dielectric material		thermoplastic										
Contacts		silver or gold plated, please order contacts separately acc. to drawing M-N 01 015 00XX X (3-8pol) or M-N 01 010 0158 X U (12-14pol)										
Termination technique		solder, crimp										
Wire gauge		2-6 pol (exclusive 5S): 0,09-1,0mm ² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm ² / 28-20 AWG									0,09-0,25mm ² / 28-24 AWG	
Flamability		UL 94 VO										
locking system	IEC 60130-9 DIN EN 61076-2-106	metal screw coupling; tightening torque 1,0 - 1,5 Nm										

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ designed acc. pollution degree 2; can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
⁴⁾ under operating conditions >10⁸ Ohm
⁵⁾ Remark for gold plated contacts: In order to avoid brittle inter-metallic connections, gold-plated terminals have to be tin-plated in the solder area.

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground. Parts according to directive 2002/95/EG (RoHS).

Montageausschnitt M1:1
Panel Cutout

	14 (14-a)	Ag	C091 31S014 100 2 U
		Au	C091 31S014 200 2 U
	12 (12-a)	Ag	C091 31S012 100 2 U
		Au	C091 31S012 200 2 U
	8 (08-a)	Ag	C091 31S008 100 2 U
		Au	C091 31S008 200 2 U
	7 (07-b)	Ag	C091 31S107 100 2 U
		Au	C091 31S107 200 2 U
	7 (07-a)	Ag	C091 31S007 100 2 U
		Au	C091 31S007 200 2 U
	6 (6-a)	Ag	C091 31S006 100 2 U
		Au	C091 31S006 200 2 U
	5 (05-b)	Ag	C091 31S105 100 2 U
		Au	C091 31S105 200 2 U
	5 (05-a)	Ag	C091 31S005 100 2 U
		Au	C091 31S005 200 2 U
	4 (04-a)	Ag	C091 31S004 100 2 U
		Au	C091 31S004 200 2 U
	3 (03-a)	Ag	C091 31S003 100 2 U
		Au	C091 31S003 200 2 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. to DIN EN 61076-2-106)	contact plating	Part number

Gewicht (errechnet) / Calc WT: 18,74 g		Zul. Abw./Tolerances:		Maßstab / Scale: 2:1; 1:1		A3	
		Prüfmaß / Testdimension				CUSTOMER DRAWING	
Teileindex Partindexnumber		Datum/Date		Name		Male receptacle	
		Gez.		Drawn		Male receptacle 6way	
		07.07.2016		RSCHÄ			
		Status: Released		Inspector: 07.07.2016 MGRIM			
		Amphenol-Tuchel Electronics GmbH					
03	201600320	07.07.2016	RSCHÄ			M	C091 31SXXX X00 2 U
Index	Änderung/Description	Datum/Date	Name	4.032.796		Ers. f. / Replacement for: M-C091 31SXXX X00 2 U Rev02	
						Blatt/Sheet 1 1 Bl.	