




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	29OCT2018	WY	SZ
	2	UPDATE SIGNAL PIN HOLE FROM 1.02 TO 0.72	15NOV2018	WY	SZ

D




- 1 "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN.
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-O
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
OF POWER AND SIGNAL CONTACTS.
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7 PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn
OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.

C




B



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

- | | |
|--------|-------|
| 0 PLC | ±. |
| 1 PLC | ±. |
| 2 PLC | ±0.15 |
| 3 PLC | ±0.05 |
| 4 PLC | ±. |
| ANGLES | ±. |

FINISH



DWN 29OCT2018

WY

CHK 29OCT2018

WY

APVD 29OCT2018

SZ

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

20S + 6P	2334531-2
DESCRIPTION	PART NUMBER



TE Connectivity

NAME
RIGHT ANGLE HEADER, SOLDER
MULTI-BEAM PLUS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2334531-2	-

SCALE	SHEET	OF	REV
1:1	1	2	2

D


C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

PART NUMBER	ROWS		SIGNLA				POWER												
			1	2	3	4	P1		P2		P3		P4		P5		P6		
2334531-2	E		P5	P5	P5	P5	TM	TN	TM	TN	TM	TN	TM	TN	TM	TN			
	D		P4	P4	P4	P4													
	C		P3	P3	P3	P3													
	B		P2	P2	P2	P2													
	A	HD	P1	P1	P1	P1												HD	
20S+6P																			



STD SOLDER TYPE SIGNAL CONTACT, ROW E	P5
STD SOLDER TYPE SIGNAL CONTACT, ROW D	P4
STD SOLDER TYPE SIGNAL CONTACT, ROW C	P3
STD SOLDER TYPE SIGNAL CONTACT, ROW B	P2
STD SOLDER TYPE SIGNAL CONTACT, ROW A	P1
STD SOLDER POWER CONTACT, RIGHT	TN
STD SOLDER POWER CONTACT, LEFT	TM
HOUSING	HOUSING
HOLD DOWN, MULTI-BEAM	HD
DESCRIPTION	IDENTIFIER

RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±0.15
3 PLC	±0.05
4 PLC	±-
ANGLES	±-
FINISH	-

MATERIAL

-

2

DWN
WY

29OCT2018

CHK
WY

29OCT2018

APVD
SZ

29OCT2018

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

RIGHT ANGLE HEADER, SOLDER MULTI-BEAM PLUS

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2334531-2

RESTRICTED TO

-

SCALE

1:1

SHEET

2 OF 2

REV

2