





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSAL DESIGN	03AUG2018	WY	SZ

- 1
- "TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN.
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2
- MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-O
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3
- CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
OF POWER AND SIGNAL CONTACTS.
- 4
- MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5
- DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6
- PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7
- PCB - .0453±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn
OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.003 HOLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WY	03AUG2018	5LP + 24S + 2P 2334570-4	
		CHK WY	03AUG2018		
		APVD SZ	03AUG2018	DESCRIPTION	
		PRODUCT SPEC	-	PART NUMBER	
		APPLICATION SPEC	-	RIGHT ANGLE RECEPTACLE, SOLDER MULTI-BEAM PLUS	
		WEIGHT	-		
CUSTOMER DRAWING		SIZE	A3	CAGE CODE	00779
		DRAWING NO	C-2334570-4	RESTRICTED TO	-
		SCALE	1:1	SHEET	1 OF 2
		REV	1		

