

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




COPYRIGHT 20

BY -





ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RPRODUCTION RELEASE	13JUN2019	JW	SH



2343987-1 AS SHOWN

DETAIL A
SCALE 8:1


- 1 CAGE ASSEMBLY: STAINLESS STEEL.
HEAT SINK: ALUMINUM/NICKEL PLATE.
HEAT SINK CLIP: STAINLESS STEEL.
EMI SPRING: COPPER ALLOY/NICKEL PLATE.
- 2 REFERENCE APPLICATION SPECIFICATION 114-32023 FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
BOARD LAYOUT PER THIS PRINT.
- 3 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 4 DATE CODE (YYWWD) MARKED APPROXIMATELY
AS SHOWN.
5. MATES WITH QSFP DD MSA COMPATIBLE TRANSCEIVER.
6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.45 MIN
DOUBLE SIDED: 2.20 MIN
- 7 ONLY FOR VERSION WITH REAR EONS
- 8 PROPOSAL ONLY

8	W/O REAR EONS	23	NET	1-2343987-3
8	W/O REAR EONS	16	SAN	1-2343987-2
8	W/O REAR EONS	13.7	PCI	1-2343987-1
	W/ REAR EONS	23	NET	2334987-3
	W/ REAR EONS	16	SAN	2343987-2
	W/ REAR EONS	13.7	PCI	2343987-1
	REMARK	DIM A	HEATSINK	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. WANG 13SEP2018	TE Connectivity	
DIMENSIONS:		CHK S. HAN 13SEP2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. HAN 13SEP2018	NAME CAGE ASSEMBLY WITH HEATSINK THRU BEZEL, 1X5, QSFPDD	
mm		PRODUCT SPEC	-	
0 PLC ±0.25		APPLICATION SPEC	-	
1 PLC ±0.25		WEIGHT	-	
2 PLC ±0.25		CUSTOMER DRAWING	SCALE 1:1	
3 PLC ±			SHEET 1 OF 6	
4 PLC ±			REV A	
ANGLES ±				
FINISH				

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




2343987-2
UNMARKED DIMENSIONS SAME AS 2343987-1
SCALE 3:2




DIM A MAX
AFTER MODULE
INSERTION





SCALE 1:1






2343987-3
UNMARKED DIMENSIONS SAME AS 2343987-1
SCALE 3:2






DIM A MAX
AFTER MODULE
INSERTION





1-2343987-1 W/O REAR EONS
DIMENSIONS SAME AS 2343987-1
SCALE 3:2




1-2343987-2 W/O REAR EONS
DIMENSIONS SAME AS 2343987-2
SCALE 3:2



1-2343987-3 W/O REAR EONS
DIMENSIONS SAME AS 2343987-3
SCALE 3:2



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. WANG 13SEP2018	 TE Connectivity			
		CHK S. HAN 13SEP2018				
		APVD S. HAN 13SEP2018				
		PRODUCT SPEC -				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CAGE ASSEMBLY WITH HEATSINK THRU BEZEL, 1X5, QSFPDD		
mm		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± FINISH		SIZE A2		
MATERIAL		-		CAGE CODE -		
		-		DRAWING NO C-2346987		
				RESTRICTED TO -		
				SCALE 1:1 SHEET 2 OF 6 REV A		
				CUSTOMER DRAWING		




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20	
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. WANG	13SEP2018
		CHK	S. HAN	13SEP2018
		APVD	S. HAN	13SEP2018
		PRODUCT SPEC	-	
		APPLICATION SPEC	-	
		WEIGHT	-	
		CUSTOMER DRAWING	-	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC	±0.25
		1 PLC	±0.25
		2 PLC	±0.25
		3 PLC	±
		4 PLC	±
		ANGLES	±
		FINISH	±
MATERIAL		-	-
		-	-

NAME		CAGE ASSEMBLY WITH HEATSINK THRU BEZEL, 1X5, QSFPDD	
SIZE		A2	
CAGE CODE		-	
DRAWING NO		C-2346987	
RESTRICTED TO		-	
SCALE		1:1	
SHEET		3 OF 6	
REV		A	





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. WANG 13SEP2018	 TE Connectivity		
DIMENSIONS: mm		CHK S. HAN 13SEP2018			
		APVD S. HAN 13SEP2018	NAME CAGE ASSEMBLY WITH HEATSINK THRU BEZEL, 1X5, QSFPDD		
		PRODUCT SPEC -	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE A2	CAGE CODE -	DRAWING NO C-2346987
0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.25 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH		WEIGHT -	RESTRICTED TO -		
MATERIAL -		CUSTOMER DRAWING	SCALE 2:1	SHEET 5 OF 6	REV A

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

