


Für diese Unterlage behalten wir uns alle Rechte vor, auch fuer den Fall der Patenterteilung oder Gebrauchsmustererteilung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfaeltigt noch sonstwie benutzt, noch Dritten zugaenglich gemacht werden.

Nur rol gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Aenderungsdienst und sind zur Fertigung freigegeben. Only red stamped or on jobcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction A
3:1





GKAW BC-P40LBC0-000L
Mechanical coding: B
Color coding: red





GKAW C-P40LBC0-000L
Mechanical coding: C
Color coding: blue



GKAW D-P40LBC0-000L
Mechanical coding: D
Color coding: green



GKAW AC-P40LBC0-000L
Mechanical coding: A
Color coding: light brown



Technical information


- Solder contacts: AWG28
- Current load: $1A \pm 40^\circ$ (Single contact)
- Test voltage: 750V (acc. SAE AS 13441:1998, Contact to contact)
- Rated voltage: 250V (acc. SAE AS 13441:1998) 2)

1) ODU recommend an additional locking of the nut with adhesive (e.g. Loctite 2701) to the screw thread.

2) Maximal operating voltage at sea level up to 2.000 m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) ! /the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

Only insert
View in direction B
5:1



		Benennung/description:		Werkstoff: material:	
Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Geraeteteil cpl. Receptacle		see BOM	
Status/state:		Version: revision:		Maßstab: Scale:	
Erstellt/prepared		spantze		4:1	
Geraendert/revised		spantze		Format: size:	
Freigabe/released		mmeier		A3	
ODU-MUEHLDOERF		Datum/date		Einheit: dim.: mm	
		Name/name		Bl.: sheet: 1	
		Benennung/description:		GKAW _C-P40LBC0-000L	
		Teile-ID: part-ID:		00101714	
		Oxaion-Nr.:		GKAW _C-P40LBC0-000L	
		Ursprung/origin.:			