




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

2

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
A			01/23/08	

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic
Flame retardant to UL94 V-0
Color Black
CONTACT: Brass, 0.4um(15u") min gold over 1.25um(50u") min Nickel
REAR NUT : Brass, 2.5um(100u") min tin over 1.25um(50u") min Nickel
ELECTRICAL : Voltage rating 300 V RMS at 50 Hz
Current rating 7.5A
Withstanding Voltage >1000 V RMS at 50 Hz for one minute
Insulation resistance >5000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 155°C
Damp heat 56 days(40 °C-95% HR)
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717TW A 7W2 P 3R

RoHS Compliance

717TW: Tin plated shell with dimples

Shell Size :A

3R=M3 rear nut

Contact type:
P=Male

Configuration: 7W2

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
	U.S. METRIC	DRAWN	Lisa.peng 01/23/08
.X	+/-	CHECKED	Hk.wang 01/23/08
.XX	+/-		
.XXX	+/-		
FRACTIONS	+/-		
ANGLES	+/-		
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		

TITLE
Hybrid connector, TW series

SIZE	DRAWING NO.	REV.
A4	C L717TWA7W2P3R	A
SCALE	NONE	SHEET 1 OF 1