

6			5		4		3		2		1	
ITEM	PART#	DESCRIPTION	QTY	UOM				FROM	TO	DESCRIPTION	COLOR	
A,B	430200400	MicroFit 3.0 Plug DR PnlMnt 4Ckt	2	PC				A1	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	
C	430310023	MICROFIT 3.0 M CRP TERM CHN 30AU 18AWG	8	PC				A2	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	
D	--	PAPER PRINTED PAPER WHITE	1	PC				A3	B4	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	
								A4	B3	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	




TABLE			
PART NUMBER	L1	L2	TITLE
2147572041	150±8	63REF	MICRO-FIT3.0 P-P 4 CIRCUIT 150MM Au
2147572042	300±10	138REF	MICRO-FIT3.0 P-P 4 CIRCUIT 300MM Au
2147572043	600±10	287REF	MICRO-FIT3.0 P-P 4 CIRCUIT 600MM Au

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
12/25/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex SEE TABLE						
	= 0	mm		NTS		EC NO: 629791 DRWN: ARAJU 2019/12/25 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18										
	= 0	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	= 0	ANGULAR TOL ± °														
	= 0	4 PLACES		±		INITIAL REVISION: DRWN: ARAJU 2019/12/25 APPR: RDESAI01 2020/01/18				PRODUCT CUSTOMER DRAWING						
	= 0	3 PLACES		±												
	= 0	2 PLACES		±						DOCUMENT NUMBER			DOC TYPE	DOC PART	REVISION	
	= 0	1 PLACE		±		2147572040				PSD	000	A				
	= 0	0 PLACES		±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	= 0									A4-SIZE		214757	SEE TABLE		GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:12
-----------------	----	--------------	------------	----------