

6		5			4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM			FROM	TO	DESCRIPTION	COLOR
A,B	430250200	MicroFit 3.0 DR Rcpt 2Ckt			2	PC			A1	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	430300038	MicroFit 3.0 F Crp Term Chn Tin 18			4	PC			A2	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
D	--	PAPER PRINTED PAPER WHITE			1	PC						




TABLE			
PART NUMBER	L1	L2	TITLE
2147551021	150±8	63REF	MICRO-FIT3.0 R-R 2 CIRCUIT 150MM Sn
2147551022	300±10	138REF	MICRO-FIT3.0 R-R 2 CIRCUIT 300MM Sn
2147551023	600±10	287REF	MICRO-FIT3.0 R-R 2 CIRCUIT 600MM Sn

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped in Flag type.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
27/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
SYMBOLS	DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex SEE TABLE											
 = 0	mm		NTS	EC NO: 629791 DRWN: ARAJU 2019/12/27 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18															
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)																		
 = 0	ANGULAR TOL ± °																		
 = 0	4 PLACES ±			INITIAL REVISION: DRWN: ARAJU 2019/12/27 APPR: RDESAI01 2020/01/18				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION							
 = 0	3 PLACES ±							2147551020		PSD	000	A							
 = 0	2 PLACES ±																		
 = 0	1 PLACE ±			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
 = 0	0 PLACES ±									A4-SIZE		214755		SEE TABLE		GENERAL MARKET		1 OF 1	
 = 0																			