







10	9	8	7	6	5	4	3	2	1
GENERAL TOLERANCE									
10 MAX	30 MAX	50 MAX	70 MAX	100 MAX	120 MAX	250 MAX	250 OVR	ANGLE	ECCENT
±0.15	±0.20	±0.30	±0.40	±0.50	±0.75	±0.90	±1.4	±0.5°	0.1



- NOTES:
1. MATERIAL: POLYESTER(PBT), GLASS FILLED, UL94V-0
 2. MATES WITH: 502352,560020, SERIES
 3. APPLICABLE TERMINAL: 560124-0101, 560124-0131
 4. APPLICABLE ISL: 560125-1200
 5. GENERAL TOLERANCES: SEE TABLE
 6. EVL AND RoHS COMPLIANT
 7. PRODUCT SPECIFICATION: PS-560123-001
 8. PACKING SPECIFICATION: PK-560123-001

ORDER NO	MATERIAL NO	COLOR
560123-1200	5601231200	WHITE
560123-1201	5601231201	BLACK

DOCUMENT STATUS	P1	RELEASE DATE	2019/03/18	01:07:46
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
▽ = 0	DIMENSION UNITS	SCALE	CURRENT REV DESC:	EC NO: 613842	DOCUMENT NUMBER	DOC TYPE	DOC PART
▽ = 0	mm	1:1	DRWN: SAKIM	2019/03/14	SD-560123-007	PSD	001
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: YKJUNG	2019/03/18			A1
▽ = 0	ANGULAR TOL ± °		APPR: YKJUNG	2019/03/18			
▽ = 0	4 PLACES ±		INITIAL REVISION:				
▽ = 0	3 PLACES ±		DRWN: SJLEE06	2015/10/27			
▽ = 0	2 PLACES ±		APPR: JYCHOI	2016/01/27			
▽ = 0	1 PLACE ±						
▽ = 0	0 PLACES ±						
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
▽ = 0							