




- Notes
- 1 Rotation examples of ref. No. ① and ② are shown.
  - 2 The recommended torque of ref. No. ⑧ : 2 to 3 N · m.
  - 3 The recommended torque of ref. No. ⑪ : 0.3 to 0.4 N · m.
  - 4 Bolting tool for ref. No. ⑪ : PB205/1.27 (CL150-0066-3)

|                                      |              |                             |            |                                            |                             |                                             |                          |
|--------------------------------------|--------------|-----------------------------|------------|--------------------------------------------|-----------------------------|---------------------------------------------|--------------------------|
|                                      |              |                             | 11         | STEEL                                      | NICKEL PLATING              | THE WIDTH ACROSS OF A HEXAGON SOCKET : 1.27 |                          |
| 5                                    | BRASS        | MATTE FINISH NICKEL PLATING | 10         | BRASS                                      | NICKEL PLATING              |                                             |                          |
| 4                                    | PPS          | (BLACK) UL94V-0             | 9          | ZINC ALLOY                                 | MATTE FINISH NICKEL PLATING |                                             |                          |
| 3                                    | PPS          | (BLACK) UL94V-0             | 8          | ZINC ALLOY                                 | MATTE FINISH NICKEL PLATING |                                             |                          |
| 2                                    | COPPER ALLOY | SILVER PLATING 5 μm min.    | 7          | BRASS                                      | NICKEL PLATING              |                                             |                          |
| 1                                    | ZINC ALLOY   | MATTE FINISH NICKEL PLATING | 6          | BERYLLIUM COPPER                           | NICKEL PLATING              |                                             |                          |
| NO.                                  | MATERIAL     | FINISH , REMARKS            | NO.        | MATERIAL                                   | FINISH , REMARKS            |                                             |                          |
| UNITS<br>mm                          |              | SCALE<br>2 : 1              | COUNT<br>1 | DESCRIPTION OF REVISIONS<br>DIS-C-00000559 |                             | DESIGNED<br>KN. IKEHARA                     | CHECKED<br>HY. KOBAYASHI |
|                                      |              |                             |            |                                            |                             | DATE<br>15. 11. 02                          |                          |
| <b>HRS</b> HIROSE ELECTRIC CO., LTD. |              |                             | APPROVED   | HY. KOBAYASHI                              | 15. 09. 10                  | DRAWING NO.<br>EDC-112329-81-00             |                          |
|                                      |              |                             | CHECKED    | HY. KOBAYASHI                              | 15. 09. 10                  | PART NO.<br>RM12BPE-6S(81)                  |                          |
|                                      |              |                             | DESIGNED   | KN. IKEHARA                                | 15. 09. 10                  | CODE NO.<br>CL109-0427-0-81                 |                          |
|                                      |              |                             | DRAWN      | KN. IKEHARA                                | 15. 09. 10                  |                                             |                          |