


TO
R

A
B
C
D
E
F

NOTES 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA.φ 1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
② THE RECOMMENDED CLAMP TORQUE,REF.NO.③ :2 TO 2.5N・m.
LOCTITE 242,HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO.③ FOR LOOSENING.



2	POLYBUTYLENE TEREPHTHALATE (BLACK)	UL94V-0	4	PHOSPHOR BRONZE	NICKEL PLATING
1	BRASS	NICKEL PLATING	3	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DRAWN	DESIGNED	CHECKED
			M. Sato	T. Horie	M. Sato
			07.03.20	07.03.20	07.03.22
					07.03.22
DRAWING NO. EDC3-027648-73			PART NO. HR10A-13TR-20SC(73)		
SCALE 2 : 1			CODE NO. CL110-1002-7-73		
UNITS mm			HRS HIROSE ELECTRIC CO., LTD		

A
B
C
D
E
F