





- NOTES 1 APPLICABLE CRIMPING CONTACT:HR22-SC-222(CL122-0008-8)
(APPLICABLE WIRE:AWG#24 TO 28, OUTER DIMENSION OF JACKET:Ø1.15MAX.)
APPLICABLE CONTACT EXTRACTION TOOL:RP6-SC-TP(CL150-0039-0)
- 2 ACROSS FLATS OF HEXAGON SOCKET OF REF.NO.12 :1.27.
THE RECOMMENDED CLAMP TORQUE OF REF.NO.12 :0.3 TO 0.4N·m.
- 3 THE RECOMMENDED CLAMP TORQUE OF REF.NO.7 AND NO.11 :2N·m.
- 4 LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF.NO.1 AND NO.12 FROM LOOSENING.
- 5 ROTATION EXAMPLES OF REF.NO.1, 7 AND 11 ARE SHOWN.
- 6 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER.
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

7	BRASS	NICKEL PLATING			
6	PHOSPHOR BRONZE	NICKEL PLATING	13	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)
5	STEEL	NICKEL PLATING	12	STEEL	NICKEL PLATING M2. 6X0. 45X2
4	BRASS	NICKEL PLATING	11	BRASS	NICKEL PLATING
3	SILICONE RUBBER	(BLACK)	10	BRASS	NICKEL PLATING
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	9	SILICONE RUBBER	(BLACK)
1	ZINC ALLOY	NICKEL PLATING	8	SILICONE RUBBER	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED :MO. SATOH	07.01.23	DRAWING NO.	EDC3-042799-73			
		CHECED :EJ. KUNII	07.01.23	PART NO.	HR22-12WTPA-20SC(73)			
		DESIGNED :HS. KAWASHIMA	07.01.23	CODE NO.	CL122-0004-7-73			
		DRAWN :MK. SATO	07.01.16					