






EKRAN PODŁĄCZONY DO OBUDOWY
SHIELD CONNECTED TO THE COUPLING NUT



EKRAN PODŁĄCZONY DO OBUDOWY
SHIELD CONNECTED TO THE COUPLING NUT




UWAGI:
1. DŁUGOŚĆ CIĘCIA I SPECYFIKACJE NABIJANIA
W LIŚCIE CIĘCIA.
2. PART LIST, BOM I KLUCZ NA DRUGIEJ STRONIE.

NOTES:
1. CUTTING LENGTHS AND CRIMPING SPECIFICATIONS
ARE ON THE CUTTING LIST.
2. PART LIST, BOM & MATRIX ON THE SECOND SIDE.

DOCUMENT STATUS	P1	RELEASE DATE	2018/12/12	14:39:34
-----------------	----	--------------	------------	----------

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
	mm		2:1							
	GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 609048 DRWN: AKONDRACIUK 2018/12/10 CHK'D: MKOWALCZYK01 2018/12/12 APPR: MKOWALCZYK01 2018/12/12			MMC-5P-5W-FE/FE-ST/ST-XM-PUR-S				
	ANGULAR TOL ± °									
	4 PLACES ±									
	3 PLACES ±									
	2 PLACES ±		INITIAL REVISION: DRWN: AKONDRACIUK 2018/12/10 APPR: MKOWALCZYK01 2018/12/12			PRODUCT DESIGN DRAWING				
	1 PLACE ±									
	0 PLACES ±		DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		1200698462		PDD		00P	A			
THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
		A3-SIZE		120069		SEE SHEET 2		GENERAL MARKET		1 OF 2

KLUCZ / PART No MATRIX



PART LIST

Lp.	MOLEX PN	ENGINEERING No	L+Tol. [mm]
1	1200698462	885S10P20M008	800 +45
2	1200698463	885S10P20M030	3000 +89
3	1200698464	885S10P20M050	5000 +165
4	1200698465	885S10P20M070	7000 +165
5			
6			
7			
8			
9			
10			
11			
12			
13			
14			
15			
16			
17			
18			
19			
20			
21			
22			
23			
24			
25			
26			
27			
28			
29			
30			
31			
32			
33			
34			
35			

TABELA 1 / TABLE 1

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE JACKET	UL	CSA	STATIC: TEMP. / BENDING RADIUS	DYNAMIC: TEMP. / BENDING RADIUS	DRAG CHAIN TESTED	SHIELD
P20	5	0.34mm ²	PUR BLACK LS0H	-	-	-30°C to +80°C	-	-	YES

BILL OF MATERIAL

8	908486995	1	LABEL	VINYL	YELLOW
7	899921504 967550297	-	OVERMOULDING	TPU	BLACK
6	1202040002	2	GASKET	FPM	RED
5	1202070007	2	COUPLING NUT FEMALE	BRASS	Nli PLATED
4	1203112809	2	SLEEVE	BRASS	Nli PLATED
3	1202080183	2	INSERT FEMALE	PUR	BLACK
2	1202060002	10	CONTACT M12 FEMALE	BRONZE	SELECTIVE GOLD OVER NICKEL
1	1202092233	-	CABLE	PUR	BLACK
ITEM	MOLEX PN	QTY.	DESCRIPTION	MATERIAL	FINISH/COLOR

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
= 0 = 0 = 0		DIMENSION UNITS mm		SCALE 1:1		CURRENT REV DESC: EC NO: 609048 DRWN: AKONDRACIUK2018/12/10 CHK'D: MKOWALCZYK012018/12/12 APPR: MKOWALCZYK012018/12/12				molex MMC-5P-5W-FE/FE-ST/ST-XM-PUR-S											
GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± °																					
= 0 = 0 = 0		4 PLACES ±				INITIAL REVISION: DRWN: AKONDRACIUK2018/12/10 APPR: MKOWALCZYK012018/12/12				PRODUCT DESIGN DRAWING DOCUMENT NUMBER1200698462 DOC TYPEPDD DOC PART00P REVISIONA											
1 PLACE ±																					
= 0 = 0		0 PLACES ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION DRAWINGA3-SIZE SERIES120069						MATERIAL NUMBER SEE MATRIX		CUSTOMER GENERAL MARKET		SHEET NUMBER 2 OF 2	