

F

E


D

C

B

A

FEMALE




OBUDOWA ZENSKA 19 POL.
WIDOK OD STRONY DRUTOW
FEMALE INSERT 19 POL.
VIEW FROM WIRES SIDE

Pin	Kolor przew.	Wire color
1	Fioletowy	VT
2	Czerwony	RD
3	Szary	GY
4	Czerwony/Niebieski	RD/BU
5	Zielony	GN
6	Niebieski	BU
7	Szary/Rozowy	GY/PK
8	Biały/Zielony	WH/GN
9	Biały/Zółty	WH/YE
10	Biały/Szary	WH/GY
11	Czarny	BK
12	Zielony/Zółty	GN/YE
13	Zółty/Brazowy	YE/BN
14	Brazowy/Zielony	BN/GN
15	Biały	WH
16	Zółty	YE
17	Rozowy	PK
18	Szary/Brazowy	GY/BN
19	Brazowy	BN


Table of lenght tolerances/ Tablica tolerancji dlugosci mm		
Over/Od	Up to and including/ Do-włącznie	Tolerance/Tolerancja +
0	305	+19
305	915	+45
915	1830	+56
1830	3660	+89
3660	7320	+165
7320	14640	+317
14640	30500	+622
30500		+2% of lenght/dlugosci

TABELA 1
CHART 1

Molex P/N:	WOODHEAD P/N:	L [mm]
1200945015	K03000B20M100	10000
1200945016	K03000B20M200	20000
1200945024	K03000B20M050	5000



WIDOK OD
STRONY CZOLA
VIEW FROM
FRONT SIDE



UWAGI:

1. DŁUGOSC CIECIA PRZEWODOW I
SPECYFIKACJE NABIJANIA W LISCIE CIECIA.

NOTES:

1. FOR WIRES CUTTING LENGTHS AND CRIMPING
SPECIFICATIONS SEE THE CUTTING LIST.

ORIGINAL RELEASE EC NO: DRWN:M.DABROWSKA 2008/11/20 CHKD: APPR: A	DESCRIPTION REV	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE 1	DESIGN UNITS	FIRST ANGLE PROJECTION			
				mm	INCH	DRAWN BY M.DABROWSKA	DATE 2008/06/16	TITLE M23-19P-FE-ST-XXM-PUR-UL					
			4 PLACES	±	±	CHECKED BY	DATE						
			3 PLACES	±	±	APPROVED BY DWARWAS		DATE 2008/06/23	MOLEX INCORPORATED				
			2 PLACES	±	±								
			1 PLACE	±	±	DOCUMENT NO. K03000B20MXXX					SHEET NO. 1 OF 1		
			ANGULAR ± °										
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART 1							
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						