




REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DETAIL A-A




DETAIL P1




DETAIL P2




DETAIL P3




DETAIL D




DETAIL E




DETAIL N




DETAIL P




DETAIL S




DETAIL F




DETAIL R




DETAIL T




DETAIL G




DETAIL V




DETAIL M




DETAIL H




DETAIL W




DETAIL J




DETAIL X




DETAIL Y




DETAIL K




DETAIL Z

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 18OCT2000	 TE Connectivity	
		CHK D. BIEVENOUR 18OCT2000		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
		0 PLC ±.1	TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH	
		1 PLC ±0.3	SIZE	
		2 PLC ±0.25	CAGE CODE	
		3 PLC ±.1	DRAWING NO	
		4 PLC ±.1	RESTRICTED TO	
MATERIAL	FINISH	ANGLES ±2°	A100779C=796634	
		SEE NOTES	SCALE 2:1	
SEE NOTES		SHEET 2 OF 3		
		REV R12		
CUSTOMER DRAWING				

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL AB



DETAIL AC

PRELIMINARY		NICKEL	TIN	7 9	DETAIL AC	25.40	5	8-796634-5
		CLAMP PLATING	CONTACT PLATING	MARKING	SPECIAL	L	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±.1 4 PLC ±.1 ANGLES ±2° MATERIAL SEE NOTES - FINISH SEE NOTES -				DWN S. WELDON18OCT2000 CHK D. BIEVENOUR18OCT2000 APVD D. BIEVENOUR18OCT2000 PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	TE TE Connectivity NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH SIZE CAGE CODE DRAWING NO RESTRICTED TO			
				A100779C=796634				
				SCALE 3:1 SHEET 3 OF 3 REV R12				