

NOTES:

1. MATERIAL AND FINISH (PLATING THICKNESS IN MICRO-INCHES):

BODY - BRASS, GOLD PLATING
 CONTACT - BRASS, GOLD PLATING
 INSULATOR - PTFE, NATURAL

2. ELECTRICAL:

- A. IMPEDANCE: 50 OHM
- B. FREQUENCY RANGE: DC - 4 GHz
- C. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS. MIN.

3. MECHANICAL:

- A. DURABILITY: 500 CYCLES MIN.
- B. TEMPERATURE RANGE: -65°C to +165°C

4) SHOWS CABLE ENTRY DIMENSIONS.





5. CRIMP CONTACT PIN WITH 0.7MM SQ.

6. CRIMP FERRULE WITH .128" HEX.


THIRD ANGLE PROJ. ☺ ↗

REVISONS

REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	24-Mar-05	--	--
B	BARREL, FERRULE AND HEAT SHRINK TUBE WERE CHANGED	24-Apr-19	11401	SC

RECOMMENDED
CABLE STRIPPING DIMENSIONSRECOMMENDED
MOUNTING HOLE

SCALE 4.000

**CUSTOMER OUTLINE DRAWING**

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
 <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES
 ± 0.05mm ± 0.1mm ± 0.2mm ± 0.3mm ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

-

REFERENCE

S.HSIEH

EAR#

REF:

CONFIGURATION LEVEL: In Work

FINISH

DRAWN

STAR

ENGINEER

S.HSIEH

APPROVED

S.HSIEH

CAD FILE

DATE

27-Apr-19

DATE

24-Mar-05

DATE

02-May-19

DWG SIZE

B

TITLE
**SMB BULKHEAD CRIMP
JACK (FOR RG-178B/U,
196A/U)**

SCALE: 6.0:1.0 SHEET 2 OF 2

ITEM NO. 121421AAA16GE5F

PART NO. 142231

Amphenol RF

www.amphenolrf.com

DRAWING NO. SMB1421AI-3GT30G-196AU-50