

4



3

2



1

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
2004
© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS 変更				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J			AI	REVISED ECR-10-019374	17SEP2010	T.T T.M






A - A




B - B
SCALE 10:1

C - C
SCALE 10:1



- 1 金めっき範囲。
- 2 FIXED NUTはトルク8kg・cmにて空回りしないこと。
- 3. 基板側のネジ”が締め付けあっていない時は、嵌合側のネジ”を締め付けなくてはならない。
- 1 Au PLATING AREA.
- 2 TORQUE:8kg・cm MIN.
- 3. WHEN THE SCREW BY THE SIDE OF BOARD IS NOT BOLTED, DON'T BOLT THE SCREW BY THE SIDE OF MATE.

3	FIXED NUT		BRASS
2	HDR HOUSING		THERMOPLASTIC POLYESTER(BLACK)
1	TAB POST	UNDER Ni,CONTACT AREA Au PL.0.3μMIN.TIN PLT.AT POST AREA.	BRASS
ITEM No.	NAME	FINISH	MATERIAL



推奨基板寸法(1.6±0.2)
RECOMMENDED P.C.BOARD DIM.(1.6±0.2)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ± 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH 仕上
MATERIAL 材料	

DWN J. AKASAKA 13FEB2004	CHK D. MITSUGI 18MAR2004	APVD S. MANABE 18MAR2004
PRODUCT SPEC 製品規格 108-5542		
APPLICATION SPEC 取付適用規格		
WEIGHT		
CUSTOMER DRAWING		

WIRE RANGE 抱合電線断面積		INSULATION DIA 被覆外径	
 Tyco Electronics		Tyco Electronics Corporation Kawasaki, Japan	
NAME 名称 40P HDR ASSY - V TYPE PC. I/O CONN.			
SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-1747053	RESTRICTED TO
SCALE 尺度 2:1		SHEET OF 1	REV A1