


Für diese Unterlage behalten wir uns alle Rechte vor, auch für den Fall der Patentierung oder Gebrauchsmusteranmeldung. Sie darf ohne unsere vorherige schriftliche Zustimmung weder vervielfältigt noch sonstwie benutzt, noch Dritten zugänglich gemacht werden.

Nur rol gestempelte oder auf Laufkarte gedruckte Dokumente unterliegen dem Änderungsdiens! und sind zur Fertigung freigegeben. Only red stamped or on jobcard printed documents are managed. These documents are approved for production.


All Rights reserved, including possible patents or trademarks. Documents shall not be provided to a third party or duplicated in any form without prior written permission.

CAD: Creo Parametric


Additional coding
View in direction B
3:1




K1AWBC-P40LBC0-0000
Mechanical coding: B
Color coding: red




K1AWC-P40LBC0-0000
Mechanical coding: C
Color coding: blue




K1AWDC-P40LBC0-0000
Mechanical coding: D
Color coding: green




K1AWAC-P40LBC0-0000
Mechanical coding: A
Color coding: light brown



Delivery condition
3:2



Only insert and earth tag
View in direction A
6:1




Technical information

- Max. cable $\varnothing 10.5\text{mm}$ (Based on cable with one braided shield)
- Solder contacts: AWG28
- Current load: $1\text{A} @ \Delta t 40^\circ$ (Single contact)
- Test voltage: 750V (acc. SAE AS 1344:1998, Contact to contact)
- Rated voltage: 250V (acc. SAE AS 1344:1998) 2)

1) For crimp information, torque, etc. see assembly instruction 010.650.001.000.002 (www.odu.de/downloads)

2) Maximal operating voltage at sea level up to 2.000 m. Rated voltage applies no other electrical safety standard. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. This must be evaluated in the frame of equipment engineering.

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

	Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015	 A PERFECT ALLIANCE.	Benennung/description: Kabelteil cpl. In-Line Receptacle		Werkstoff: material: see BOM
			CAD-Nr.: design-ID: 00101681		Maßstab: scale: 4:1
Status/state: Approved	Version: revision: -	Erstellt/prepared 13.01.2016 prock	Teile-ID: part-ID:		Format: size: A3
Geaendert/revised 13.01.2016 prock	Freigabe/released 29.01.2016 mmeier	Oxaion-Nr.: K1AW_C-P40LBC0-0000		Einheit: dim.: mm	
ODU-MUEHLDORF	Datum/date	Name/name	Ursprung/origin.:		Bl.: sheet: 1