




NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01), NATURAL.
UV STABILIZED NYLON (RMS-46), BLACK.
BY SPECIAL ORDER.
FLAME RETARDANT NYLON (RMS-75), NATURAL.
BY SPECIAL ORDER.
2. MIN. LOOP TENSILE: 18 LBS (80 NEWTONS).
3. MAX. BUNDLE DIAMETER: 3/4 (19.1).

E SEE CO 200134 FOR CHANGES SK 02.28.08			TITLE: SELF MOUNT WRAP-IT-TIES						DWG IN IN (MM)			
D SEE ECN #565 FOR CHANGES SM 01.23.03			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=1°		FILE # WIT-18R2A		DWN: S.M.		APP:		FINAL	
C COMPLETELY RE-DRAWN; NEW NOTES AND CHANGED FILE NO. SM 03.15.01					MAT'L: SEE NOTES		DT: 03/15/01		DT:		PART #	
B DIM (4.75±.08) WAS (4.75±.8) JL 6/10/99					RE: RICHCO, INC.		RICHCO INC. PO BOX 804238, CHICAGO, 60680		WIT-18R2A-4-01		PRINT TYPE	
A REMOVED TABLE & CORRECTED PART# AM 5/6/99							(773) 539-4060				CA	
REV DESCRIPTION ENGR DATE												