

6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM	FROM		TO	DESCRIPTION	COLOR
A,B	430200200	MicroFit 3.0 Plug DR PnlMnt 2Ckt			2	PC	A1		B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	430310021	MICROFIT 3.0 M CRP TERM CHN TIN 18AWG			4	PC	A2		B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
D	--	PAPER PRINTED PAPER WHITE			1	PC					





TABLE			
PART NUMBER	L1	L2	TITLE
2147571021	150±8	63REF	MICRO-FIT3.0 P-P 2 CIRCUIT 150MM Sn
2147571022	300±10	138REF	MICRO-FIT3.0 P-P 2 CIRCUIT 300MM Sn
2147571023	600±10	287REF	MICRO-FIT3.0 P-P 2 CIRCUIT 600MM Sn

- NOTES
1. Cable assembly must pass 100% continuity and polarity test.
 2. Connector view shown is from mating side.
 3. Label text must be 2mm max. in height with Arial font.
 4. Label must be wrapped in Flag type.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
12/27/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex SEE TABLE	
 = 0	mm		NTS		EC NO: 629791 DRWN: ARAJU 2019/12/27 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18					
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)									
 = 0	ANGULAR TOL ± °									
 = 0	4 PLACES ±		INITIAL REVISION: DRWN: ARAJU 2019/12/27 APPR: RDESAI01 2020/01/18				PRODUCT CUSTOMER DRAWING			
 = 0	3 PLACES ±									
 = 0	2 PLACES ±									
 = 0	1 PLACE ±		DOCUMENT NUMBER 2147571020						DOC TYPE PSD	DOC PART 000
 = 0	0 PLACES ±									
 = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER
 = 0					A4-SIZE	214757	SEE TABLE		GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:09
-----------------	----	--------------	------------	----------