


PART NO.	DIM. "A"
WIT-18RA-4-01	1/4" (6.4)
WIT-18RA-6-01	3/8" (9.5)
WIT-18RA-8-01	1/2" (12.7)



NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01), NATURAL.
UV STABILIZED NYLON (RMS-46), BLACK.
BY SPECIAL ORDER.
FLAME RETARDANT NYLON 6/6 UL94 V-0 (RMS-75), NATURAL.
BY SPECIAL ORDER.
2. MIN. LOOP TENSILE: 18 LBS (80 NEWTONS).
3. MAX. BUNDLE DIAMETER: 3/4 (19.1).

3. MAX. BUNDLE DIAMETER: 3/4" (19.1)			TITLE: SELF MOUNT WRAP-IT-TIES						DWG IN IN (MM)	
D	SEE CO 200134 FOR CHANGES	SK 02.28.08	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # WIT-18RA MAT'L: SEE NOTES	DWN: S.M. DT: 03/15/01	APP: DT:	FINAL			
C	COMPLETELY RE-DRAWN; NEW NOTES AND CHANGED FILE NO.	SM 03.15.01		RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		PART #	WIT-18RA-SERIES		PRINT TYPE
B	ADDED NOTE 6.	SM 02.23.01								CA
A	MAT'L UV NYLON (RMS-46) ADDED	JL 01.18.00								
REV	DESCRIPTION	ENGR DATE								

TOLERANCES
UNLESS NOTED

.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE #

WIT-18RA

DWN: S.M.

APP:

DT: 03/15/01

DT:

RE:

RICHCO, INC.
PO BOX 804238, CHICAGO, 60680
(773) 539-4060



WIT-18RA-SERIES

PRINT TYPE

CA