

6		5		4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM		FROM	TO	DESCRIPTION	COLOR
A	430200200	MicroFit 3.0 Plug DR PnlMnt 2Ckt			1	PC		A1	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
B	430310021	MICROFIT 3.0 M CRP TERM CHN TIN 18AWG			2	PC		A2	--	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	--	PAPER PRINTED PAPER WHITE			1	PC					





TABLE			
PART NUMBER	L 1	L 2	TITLE
2147581021	150±8	63REF	MICRO-FIT3.0 P-S 2 CIRCUIT 150MM Sn
2147581022	300±10	138REF	MICRO-FIT3.0 P-S 2 CIRCUIT 300MM Sn
2147581023	600±10	287REF	MICRO-FIT3.0 P-S 2 CIRCUIT 600MM Sn

NOTES

- Connector view shown is from mating side.
- Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.39mm Max.
- Label text must be 2mm max. in height with Arial font.
- Label must be wrapped in Flag type.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
30/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex			
 = 0	mm	NTS										
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)											
 = 0												
 = 0	ANGULAR TOL ± °			EC NO: 629791			SEE TABLE					
 = 0	4 PLACES		±	DRWN: ARAJU								

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:14
-----------------	----	--------------	------------	----------