

6			5		4	3	2		1	
ITEM	PART#	DESCRIPTION	QTY	UOM			FROM	TO	DESCRIPTION	COLOR
A,B	430250400	MicroFit 3.0 DR Rcpt 4Ckt	2	PC			A1	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	430300038	MicroFit 3.0 F Crp Term Chn Tin 18	8	PC			A2	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
D	--	PAPER PRINTED PAPER WHITE	1	PC			A3	B4	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
							A4	B3	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2147551041	150±8	63REF	MICRO-FIT3.0 R-R 4 CIRCUIT 150MM Sn
2147551042	300±10	138REF	MICRO-FIT3.0 R-R 4 CIRCUIT 300MM Sn
2147551043	600±10	287REF	MICRO-FIT3.0 R-R 4 CIRCUIT 600MM Sn

- NOTES
1. Cable assembly must pass 100% continuity and polarity test.
 2. Connector view shown is from mating side.
 3. Label text must be 2mm max. in height with Arial font.
 4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
27/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			
▽ = 0		mm		NTS		molex SEE TABLE			
▽ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)							
▽ = 0		ANGULAR TOL ± °							
▽ = 0		4 PLACES ±							
▽ = 0		3 PLACES ±				EC NO: 629791			
▽ = 0		2 PLACES ±				DRWN: ARAJU 2019/12/27			
▽ = 0		1 PLACE ±				CHK'D: RDESAI01 2020/01/18			
▽ = 0		0 PLACES ±				APPR: RDESAI01 2020/01/18			
☒ = 0						INITIAL REVISION:			
■ = 0						DRWN: ARAJU 2019/12/27			
▽ = 0						APPR: RDESAI01 2020/01/18			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A4-SIZE		214755	
						MATERIAL NUMBER		CUSTOMER	
						SEE TABLE		GENERAL MARKET	
								SHEET NUMBER	
								1 OF 1	