




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	JAN15/19	L.CHAN




FRONT VIEW



SIDE VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

1. MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
PLATING: GOLD ON MATING SURFACES
(SEE PART NO. FOR THICKNESS).
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ" [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH MATTE TIN PLATING ON SOLDER TAIL

PART NUMBER: RJHSE-X180

GOLD PLATING
E=RJ45 FLAT CONTACT 6u"
G=RJ45 FLAT CONTACT 15u"
J=RJ45 FLAT CONTACT 30u"
5=RJ45 FLAT CONTACT 50u"

UNLESS SPECIFIED OTHERWISE		DRAWN	W.QIU	DATE	JAN15/19	Amphenol Canada Corp. Commercial Products	
PRIMARY UNITS	INCH	CHECKED	L.CHAN	DATE	JAN15/19		
SECONDARY UNITS	MILLIMETER	M.E. APP'D				TITLE HIGH SPEED, RJ45, MODULAR JACK, 8P8C, SHIELDED WITH TABS AND COVER LED AREA- RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D					
GENERAL TOLERANCES		DWG APPR.				DWG. NO. P-RJHSE-X180	
1 DECIMAL PLACE	±0.025	ENG. REL. NO.					
2 DECIMAL PLACES	±0.020	REF.				CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	
3 DECIMAL PLACES	±0.015	THIRD ANGLE PROJECTION					
ANGULAR DEGREES	±1.0°	DO NOT SCALE DRAWING				REV A	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.