

ITEM	PART#	DESCRIPTION	QTY	UOM
A,B	430250600	MicroFit 3.0 DR Rcpt 6Ckt	2	PC
C	430300040	MicroFit 3.0 F Crp Term Chn 30Au 18	12	PC
D	---	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	B3	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A2	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A3	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A4	B6	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A5	B5	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
A6	B4	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2147552061	150±8	63REF	MICRO-FIT3.0 R-R 6 CIRCUIT 150MM Au
2147552062	300±10	138REF	MICRO-FIT3.0 R-R 6 CIRCUIT 300MM Au
2147552063	600±10	287REF	MICRO-FIT3.0 R-R 6 CIRCUIT 600MM Au

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
24/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			
 = 0		mm		NTS		EC NO: 629791 DRWN: ARAJU 2019/12/24 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18			
 = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)							
 = 0		ANGULAR TOL ± °							
 = 0		4 PLACES		±					
 = 0		3 PLACES		±		SEE TABLE			
 = 0		2 PLACES		±					
 = 0		1 PLACE		±					
 = 0		0 PLACES		±					
 = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A4-SIZE		214755	
						MATERIAL NUMBER		CUSTOMER	
						SEE TABLE		GENERAL MARKET	
								SHEET NUMBER	
								1 OF 1	