




Electrical Characteristics

Nominal Impedance:	50 ohms
Frequency Range:	DC to 4 GHz
Insertion Loss:	0.2 dB at 3 GHz
Operating Voltage (rms):	500 V maximum at sea level
Dielectric Withstand Voltage (rms):	1500 V maximum at sea level
Contact Resistance:	1.5 milliohms maximum
Insulation Resistance:	5000 megohms minimum

Mechanical Characteristics

Mating Cycles:	500 cycles minimum
Interface Dimensions:	Conform to MIL-C-39012


Environmental Characteristics

Temperature Range:	-65 °C to +165 °C
--------------------	-------------------

PART	DESCRIPTION
1	Body
2	Nut
3	Washer
4	Insulator
5	Ground Tag
6	Contact

Dimensional changes	MS	5	23 Jul 14
Dimensional changes	MS	4	7 Jan 09
Dimensional changes	SN	3	22 Nov 01
CAD Issue	SN	2	06 Nov 01
First Issue	AT	1	13 Feb 96
DESCRIPTION OF REVISION	APPVD	ISS	DATE

MOUNTING HOLE



SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:

± 0.2mm unless otherwise stated

DRAWN BY:

S Nash

CHECKED BY:

M Nielsen

APPROVED BY:

P Couzens

DATE:

22 Nov 01

TITLE:

Isolated BNC Panel Mount
Jack

PART NUMBER:

VB11094A

PAGE: 1 of 1



11 Bilton Road,
Chelmsford Essex,
CM1 2UP, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938