




- NOTES
- ① ACROSS FLATS HEXAGON HEAD OF REF.NO.10 AND 11 : 1.27.
 - ② THE RECOMMENDED CLAMP TORQUE, REF.NO.9 : 2N・m. LOCTITE 263, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO.9 FROM LOOSENING.
 - ③ THE RECOMMENDED CLAMP TORQUE, REF.NO.10 AND 11 : 0.3 TO 0.4 N・m.
4. ONE EXAMPLE OF THE ROTATION OF REF.NO.1 AND 9 IS SHOWN.

7	Brass	Nickel plating			
6	Brass	Nickel plating	13	Brass	
5	Silicone rubber	(Black)	12	Acrylonitrile-butadiene rubber	(Black)
4	Beryllium copper	Silver plating	11	Steel	Nickel plating M2.6×0.45×3
3	Beryllium copper	Silver plating	10	Steel	Nickel plating M2.6×0.45×2
2	Polybutylene terephthalate	(Black) UL94V-0	9	Brass	Nickel plating
1	Zinc alloy	Nickel Plating	8	Silicone rubber	(Black)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm					
SCALE 2 : 1		COUNT △	DESCRIPTION OF REVISIONS		
DESIGNED EJ. KUNII		16.02.13	DRAWING NO. EDC-045419-73-00		
CHECKED EJ. KUNII		16.02.13	PART NO. HR22-12TJD-20S(73)		
DESIGNED SJ. SHIMIZU		16.02.13	CODE NO. CL122-0023-1-73		
DRAWN SJ. SHIMIZU		16.02.13			