




- Notes
- 1 The recommended clamp torque of ref. No. ⑩ : 0.2 to 0.3 N·m. LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref. No. ⑩ from loosening.
 - 2 Rotation of ref. No. ⑥ to ref. No. ① is shown.
 - 3 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.

5	BRASS	NICKEL PLATING	10	BRASS	NICKEL PLATING	M2. 6×0. 45×2		
4	PPS	(BLACK) UL94V-0	9	PHOSPHOR BRONZE	NICKEL PLATING			
3	PPS	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING	JIS B 1101 M2×0. 4×10		
2	COPPER ALLOY	SILVER PLATING 2 μm.	7	BRASS	NICKEL PLATING			
1	BRASS	NICKEL PLATING	6	BRASS	NICKEL PLATING			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00000841	DESIGNED KN. IKEHARA	CHECKED HY. KOBAYASHI	DATE 16. 03. 02
HIROSE ELECTRIC CO., LTD.		APPROVED	HY. KOBAYASHI		15. 11. 06	DRAWING NO. EDC-028025-81-00		
		CHECKED	HY. KOBAYASHI		15. 11. 06	PART NO. RM15TP-4SA(81)		
		DESIGNED	KN. IKEHARA		15. 11. 06	CODE NO. CL109-0846-3-81		
		DRAWN	KN. IKEHARA		15. 11. 06			