


Feb. 1. 2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 THIS PRODUCT IS DELIVERED DISASSEMBLED.
 - 2 APPLICABLE CRIMP CONTACT AND TOOLS.

CONTACT NO.		2, 11, 12	1, 3, 4, 5, 6, 7, 8, 9, 10
APPLICABLE CRIMP CONTACT	LOOSE PIECE CONTACT	RP17-SC-212 (CL113-0509-2) SILVER PLATING 4 μm min.	RP17-SC-222 (CL113-0510-1) SILVER PLATING 4 μm min.
	SIZE	AWG#18 TO #22	AWG#24 TO #30
APPLICABLE WIRE	JACKET OUTER DIAMETER	MAX φ 1.7	MAX φ 1.2
	CONTACT EXTRACTION TOOL	RP6-SC-TP	
MANUAL CRIMPING TOOL		RP17-TC-01	

- 3 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

3	POLYCARBONATE	(BLACK) UL94V-0	6	BRASS	BLACK CHROMATE TREATMENT (TRIVALENT CHROMIUM)
2	POLYCARBONATE	(BLACK) UL94V-0	5	POLYVINYLCHLORIDE	(BLACK)
1	POLYCARBONATE	(BLACK) UL94V-0	4	BRASS	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.				APPROVED : EJ. KUNII 13. 11. 18 CHECKED : HT. ZENBA 13. 11. 18 DESIGNED : HK. NAMAI 13. 11. 18 DRAWN : HK. NAMAI 13. 11. 18	DRAWING NO. EDC3-040741-71 PART NO. RP17-13JA-12SC(71) CODE NO. CL113-0516-8-71		