











Jun.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- △△ NOTES
1. APPLICABLE WIRE IS AWG #14~#15.
INSULATION DIAMETER ϕ 3.30mm MAX.
WHEN CRIMPING AWG#14 (UL1015 ϕ 3.80mm),
DUE TO THE DESIGN OF INSULATION BARREL,
THE SHAPE OF CRIMP DOES NOT COVER INSULATION.
IT DOES NOT AFFECT THE PRODUCT QUALITY.
REFER TO ATAI-E2926 FOR CRIMP QUALITY STANDARDS.
 2. APPLICABLE CRIMPING MACHINE AND CRIMPING CONDITIONS
(CRIMP HEIGHT etc.) WILL BE SPECIFIED ACCORDING TO
AWG # OR WIRE APPLIED.
 3. ONE PACKAGE CONSISTS OF 100 PCS.

					1COPPER ALLOY		CONTACT AREA : GOLD PLATING0.2μm MIN. TERMINAL AREA : TIN PLATING1μm MIN. UNDER PLATING : NICKEL PLATING0.5μm MIN.						
NO.	MATERIAL		FINISH . REMARKS			NO.	MATERIAL		FINISH . REMARKS				
UNITS mm			SCALE 5 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-E-004877		DESIGNED TY. MIURA		CHECKED AH. KODAMA		DATE 13. 12. 20	
 HIROSE ELECTRIC CO., LTD.		APPROVED : RI. TAKAYASU			12. 12. 11		DRAWING NO. EDC3-128190-00						
		CHECKED : AH. KODAMA			12. 12. 11		PART NO. PQ50-15SCA						
		DESIGNED : TY. MIURA			12. 12. 10		CODE NO. CL236-2043-0-00						
		DRAWN : TY. MIURA			12. 12. 10		 						
5				6				7				8	