

REVISIONS REV DESCRIPTION DATE APPRD PROPOSAL DRAWING (EAR 13120) MAY17/07 K.L.

.125 [3.18]

ø.106 [ø2.69] HOLE FOR UP





NOTES:

Α

MATERIALS: ALL MATERIALS ARE ROHS COMPLIANT PER

EU DIRECTIVE 2002/95/EC AND AMENDMENTS.

SHELLS: STAMPED STEEL, TIN PLATED.

INSERT: HIGH TEMPERATURE RESISTANT THERMOPLASTIC, GLASS

REINFORCED, FLAMMABILITY RATING UL94V-0, BLACK.

CONTACT: COPPER ALLOY, 30µ" [0.76 MICRONS] GOLD PLATED


OVER 50µ" [1.27 MICRONS] MINIMUM NICKEL.

STEEL. NICKEL OR ZINC PLATED OR STAINLESS STEEL. SCREWS:

CONTACT RESISTANCE: 5 MILLIOHMS MAX.

CURRENT RATING: 20 AMPERES MAX.

INSULATION RESISTANCE: 3000 MEGAOHMS MIN.



DATE MAY17/07



CHECKED	Amphenol Canada Cor	р
DESIGNED		
APPROVED	FCE17 SERIES COMBO D-SUB CONNECTOR, 2	
INDUSTRIAL ENG. APPRD.	ARRANGEMENT, SOCKET POWER CONTACTS, SC TERMINATION FOR 12AWG WIRE, THROUGH HO	
ENGINEERING RELEASE NO.	MOUNTING, NON-FILTERED, ROHS COMPLIAN	ΙT
REF. EAR 13120  DIMENSIONS ARE IN CODE IDENT. NO.	DWG DRAWING NO. C P-FCE17-E2W2SS-2NO	RE A

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

В

С

D

INCHES [mm]

DRAWN K. LAMBIE

03554 SCALE

—— SHEET 1 OF