



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Jun-28-2017	Flan	Tommy



KEY POS	PART NUMBER	
	-40°C ~ 105°C	-40°C ~ 125°C
N	RT061823SNHSS	RT061823SNH03SS
W	RT061823SWHSS	RT061823SWH03SS
X	RT061823SXHSS	RT061823SXH03SS
Y	RT061823SYHSS	RT061823SYH03SS
Z	RT061823SZHSS	RT061823SZH03SS

- NOTES :
1. MATERIAL :
- SHELL : ZINC ALLOY , NICKEL PLATED.
- INSERT : THERMOPLASTIC , UL94 V-0.
- COUPLING NUT : AL ALLOY , NICKEL PLATED.
- SEAL GASKET : SILICONE RUBBER.
- O-RING : NBR/SILICONE RUBBER.
2. SPECIFICATIONS :
- 2.1 RATED CURRENT : 13A (MAX).
- 2.2 RATED VOLTAGE : 300V (AC/DC).
- 2.3 OPERATING TEMPERATURE : SEE CHART.
- 2.4 DIELECTRIC WITHSTANDING VOLTAGE : LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@2000 VOLTS AC.
- 2.5 INSULATION RESISTANCE : 5000 MEGOHMS MIN.
- 2.6 IP--CLASS : IP67 AND IP69K.
- 2.7 MATING CYCLES DURABILITY : 500 CYCLES MIN.
- 2.8 RoHS COMPLIANT.
3. SUITABLE CONTACTS : 16# CONTACTS.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

QUANTITY		SEE PART NUMBER CHART		DESCRIPTION		ITEM		
PART NUMBER								
MATERIALS LIST								
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN MILLIMETERS. 1) PL DEC 40.30 Fractions 1/164 3 PL DEC 40.08 Angles 1° 3) Note reference = 		SIGNATURES		DATE		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036		
		DRAWN:		Ben			Jun-28-2017	
		CHECKED:		Tod			Jun-28-2017	
		ENGINEER:						
		APPROVAL:		Tommy			Jun-28-2017	
MATERIAL SPECIFICATIONS:		CUSTOMER:		THIS DRAWING IS SUBMITTED FOR INFORMATION ONLY. IT DOES NOT CONSTITUTE A CONTRACT. SPECIFICATIONS AND PERFORMANCE DATA ARE FOR REFERENCE ONLY. NO PARTS OR REPRODUCTION ARE LIABLE. ALL MANUFACTURING VARIATIONS.				
PROCESS SPECIFICATIONS:		SIZE		TYPE	DWG NO.	REVISION		
NEXT ASSY:		B		C-	RT061823S*H*SS	A1		
		SCALE		NONE	SHEET 1	OF 1		
RT PLUG SOCKET, 23POS, SIZE 18								