







PRODUCT NO.
10150098-3200RLF

PCB LAYOUT PROPOSAL



Package Description:
1. External diameter of Reel: Ø330
2. Leader 400mm/ Trailer 160mm
3. Packageing unit: 400 pcs/Reel

Reel off direction



Note

1. Material:

- 1.1 Housing and Cap: LCP 30%GF, E130I Black, Ticona
- 2.1 Terminal and shield: CuSn6
- 2.2 Plating: 1-3µm Ni under plating, 2-4µm Sn on solder area, 0.65 µm PdNi, 0.10µm Au on mating area.
3. Coplanarity area of Termination 0.10mm Max


Inspection level 1: control chart required

Proof of process capability or 100% test if process capability is not achieved

Inspection level 2 and 3: control chart required

Proof of mean value, standard deviation and machine capability

Proof of values or proof of attributive test

spec ref *				dr	Li-Qing Lei	2018/11/26	projection  mm 	size	A3	scale	5:1			
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Li-Qing Lei	2020/06/04		ecn no	-					
				chr	-	-								
				appr	Tim Yao	2020/06/04		product family				rel level	Released	
surface	linear	0.X	±0.20	Amphenol FCi	title	Male 4mm SMD 32 pos Microspeed Vertical Series				dwg no	10150098		rev	A
		0.XX	±0.10											
		0.XXX	±0.05											
ASME Y14.5	angular	0°	±2°		cat. no.	Product - Customer Drw				sheet 1 of 1				