






This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer Drawing



Dimensions

Positions	A	B	C	E	F
09	30.81	24.99	16.92	11.08	19.20
15	39.20	33.30	25.25	19.39	27.70
25	53.05	47.04	38.96	33.24	41.10
37	69.40	63.50	55.42	49.86	57.30



50 Positions

REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	01/04/08	IP
2	HK--	Update the Drawing	11/26/13	IP
3	HK--	Define the specific material	04/23/14	IP
4	HK--	Add one dimension	10/28/14	IP
5	HK--	Add retention force	05/12/15	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" Tin over 50u" min Nickel over 50u" min Copper
BODY : Front housing: PBT, UL94V-0, Color Black
Back housing: PA66, UL94V-0, Color Black
FRONT NUT : Brass, Nickel Plated.
ELECTRICAL : Withstanding Voltage >1000 V RMS
Insulation resistance >1000 M Ohms
MECHANICAL : Terminal retention force, 2.27kg Min.
MARKING : Amphenol Logo

PRODUCT CODE

L 777 RR X XX P VF

L: RoHS Compliance

777: tinned shell +
dimples for plug

Shell Size :E,A,B,C,D

Front mounting type:
VF=fixed front
screwlock 4-40

Contact type:
P: Pin

Configuration:
09,15,25,37,50

UNLESS OTHERWISE SPECIFIED	
TOLERANCES	
U.S.	METRIC
.X +/-	0.50
.XX +/-	0.30
.XXX +/-	0.20
FRACTIONS +/-	5°
ANGLES +/-	
FOR MATERIALS AND FINISHES SEE NOTES	
REMOVE SHARP EDGES	
DIMENSIONS	
U.S.	INCHES
METRIC	MM

APPROVAL		DATE
DRAWN	Pelita Liu	05/12/16
CHECKED	Tony Tang	05/12/16
CHECKED		
DRAWING FILE :		
ANGLE OF PROJECTION		

Amphenol

Amphenol East Asia Limited

TITLE
Stamped and formed contact,RR series

SIZE	DRAWING NO.	REV.
A4	L777RRXXXPVF	5
SCALE	SHEET 1 OF 1	
NONE		