






This document is the property of Amphenol Aorora Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Aorora Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

NOTE:
1. ALL MATERIAL MUST BE COMPLY WITH SS-00259 OR RoHS.
2. "▽" MARK IS IMPORTANT DIMENSIONS
3. "▽" MARK IS CPK AND X-R DIMENSION
4. PART NO. LEGEND:
F32*-1A**1-110**

REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	/	New version	May 2014-07-28	Rain 2014-07-28	Hongkui.Liu 2014-07-28
B	/	Add new dimension	May 2014-12-24	Rain 2014-12-24	Hongkui.Liu 2014-12-24
C	/	Unified FFC dimension	May 2019-01-19	Rain 2019-01-19	Hongkui.Liu 2019-01-19

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	SLIDER	GLASS FILLED PA9T, UL94V-0	BLACK	1
2	HOUSING	GLASS FILLED LCP, UL94V-0	NATURAL	1
3	ANCHOR-PLATE	BRASS, T=0.20mm	SURFACE PLATING:2~5 um Sn UNDER PLATING:1~3 um Ni	2
4	CONTACT	PHOSPHOR BRONZE, T=0.20mm	SURFACE PLATING:SEE "NOTE" UNDER PLATING:1~3 um Ni	N



3D VIEW.

DIMENSION LIST:

NO. OF POS.	A	B	C	NO. OF POS.	A	B	C
4	6.80	1.50	2.50	33	21.30	16.00	17.00
5	7.30	2.00	3.00	34	21.80	16.50	17.50
6	7.80	2.50	3.50	35	22.30	17.00	18.00
7	8.30	3.00	4.00	36	22.80	17.50	18.50
8	8.80	3.50	4.50	37	23.30	18.00	19.00
9	9.30	4.00	5.00	38	23.80	18.50	19.50
10	9.80	4.50	5.50	39	24.30	19.00	20.00
11	10.30	5.00	6.00	40	24.80	19.50	20.50
12	10.80	5.50	6.50	41	25.30	20.00	21.01
13	11.30	6.00	7.00	42	25.80	20.50	21.51
14	11.80	6.50	7.50	43	26.30	21.00	22.01
15	12.30	7.00	8.00	44	26.80	21.50	22.51
16	12.80	7.50	8.50	45	27.30	22.00	23.01
17	13.30	8.00	9.00	46	27.80	22.50	23.51
18	13.80	8.50	9.50	47	28.30	23.00	24.01
19	14.30	9.00	10.00	48	28.80	23.50	24.51
20	14.80	9.50	10.50	49	29.30	24.00	25.01
21	15.30	10.00	11.00	50	29.80	24.50	25.51
22	15.80	10.50	11.50	51	30.30	25.00	26.01
23	16.30	11.00	12.00	52	30.80	25.50	26.51
24	16.80	11.50	12.50	53	31.30	26.00	27.01
25	17.30	12.00	13.00	54	31.80	26.50	27.51
26	17.80	12.50	13.50	55	32.30	27.00	28.01
27	18.30	13.00	14.00	56	32.80	27.50	28.51
28	18.80	13.50	14.50	57	33.30	28.00	29.01
29	19.30	14.00	15.00	58	33.80	28.50	29.51
30	19.80	14.50	15.50	59	34.30	29.00	30.01
31	20.30	15.00	16.00	60	34.80	29.50	30.51
32	20.80	15.50	16.50				

	FPC	FFC
M	0.5± 0.05	0.5± 0.05
P	0.5± 0.03	0.5± 0.03
B	B± 0.05	B± 0.05
W	W± 0.05	W± 0.05
Wp	0.35± 0.03	0.30± 0.03

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION	
X.	± 0.50	X. *	$\pm 1'$		
X.X	± 0.30	X.X *	$\pm 0.5'$		
X.XX	± 0.20	X.XX *	$\pm 0.5'$		
X.XXX	± 0.10	X.XXX *	$\pm 1'$		
LINEAR DIMS		ANGLES DIMS		DOC TYP	Customer Drw
P/N: F32Q-1A7*1-110**		F32T-1A7*1-110**		DRAWN DATE	May 2019-01-19
MATERIAL		SEE NOTES		DESIGN DATE	May 2019-01-19
FINISHED		SEE NOTES		CHECKED DATE	Rain 2019-01-19
				APPROVED DATE	Hongkui.Liu 2019-01-19



Amphenol Aorora Technology (Huizhou) Co.,Ltd

TITLE: FPC P0.5 CONN ZIF R/A TYPE SMT (UPPER CONTACT)

SIZE DWG NO. A4 A-S0200

SCALE 1:1 UNIT : mm SHEET 1 OF 1

