

Customer Information


IF IN DOUBT - ASK DRAWING No.: M80-263FIXX-XX-XX NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm



	/EXAMPLE CONFI / M80-263F106-0	
EXAMPLE CONFIGURATION: M80-263F102-10-01		
9 1		
SECTION Y-Y		
	NOTES:	
7.55 MAX	 CONNECTORS ARE SUPPLIED WITHOUT CONTACTS SUITABLE FOR FEMALE CABLE POWER, COAXIAL DATAMATE CONTACTS - FOR MORE INFORMATION 	AND SIGNAL
	HARWIN.COM. 3. FOR MECHANICAL AND ELECTRICAL SPECIFICAT SPECIFICATION COO5XX (LATEST ISSUE).	ION SEE COMPONENT

DIMENSION	CALCULATIONS	
DIM 'A'	((4 x No. OF SPECIAL CONTACTS) + No. OF SIGNAL CONTACTS) + 10.0	
DIM 'B'	((4 x No. OF SPECIAL CONTACTS) + No. OF SIGNAL CONTACTS) + 5.0	
EXAMPLES: CONNECTOR WITH 02 RIGHT (BEFORE No.1) SPECIAL CONTACTS, 10 SIGNAL CONTACTS AND 01 LEFT (AFTER No.1) SPECIAL CONTACTS, M80-263F102-10-01 DIM 'A' = 32.0mm, DIM 'B' = 27.0mm		
	CONNECTOR WITH NO SIGNAL CONTACTS, AND 06 SPECIAL CONTACTS, M80-263F106-00-00 DIM 'A' = 34.0mm, DIM 'B' = 29.0mm	





www.harwin.com technical@harwin.com THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

X. = ±1mm X.X = ±0.50mm $X.XX = \pm 0.20$ mm $X.XXX = \pm 0.01$ mm ANGLES = ±5°

UNLESS STATED

TOLERANCES MATERIAL:

SEE ABOVE FINISH: SEE ABOVE

S/AREA:

JACKSCREW DATAMATE MIXED TECHNOLOGY FEMALE CRIMP MOULDING WITH HARDWARE

DRAWING NUMBER:

M80-263FIXX-XX-XX

OF _