



PCB LAYOUT



APPLICATION VIEW



FULLY MATED ASSMEBLY

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APPD
A	NEW RELEASE	MAR27/20	S.M.
B	XX OPTIONS ADDED	JUN16/20	S.M.

NOTES:

- MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU & AMENDMENTS
 - HOUSING: ENGINEERING THERMOPLASTIC, UL FLAMMABILITY RATING 94V-0, COLOUR BLACK
- ELECTRICAL CHARACTERISTICS
 - CURRENT RATING: 7A (18 AWG) OR 5A (20 AWG) OR 3A (22 AWG) PER CONTACT
 - DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC
 - INSULATION RESISTANCE: 500 MEGAOHMS
 - OPERATING TEMPERATURE: -40 °C TO +105 °C

AMPHENOL PART NUMBER: **FLM-P22-XX**

XX = 00 - BLACK HOUSING (STANDARD)
 XX = W0 - WHITE HOUSING
 XX = 01-99 CUSTOM CONFIGURATIONS

UNLESS SPECIFIED OTHERWISE	DRAWN	S.MUGAN	MAR27/20
PRIMARY UNITS MILLIMETERS	CHECKED	A.GREEN	MAR27/20
SECONDARY INCHES	M.E. APPD		
REFERENCE IN PARENTHESES	Q.A. APPD		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.		
2 DECIMAL PLACES ±0.10	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	DO NOT SCALE DRAWING		

Amphenol Canada Corp.
 Commercial Products
 FLM SERIES,
 RECEPTACLE BOARD MOUNT-SMT
 RoHS COMPLIANT

DWG. NO.	REV
P-FLM-P22-XX	B
CODE ID NO. 03554	DWG SIZE: X
SCALE: 5:1	SHEET 1 OF 1