



PC BOARD LAYOUT

NOTE :
 RATING:
 VOLTAGE RATEING : 30V AC (rms)
 CURRENT RATING : 1 A MAX
 ELECTRICAL CHARACTERISTICS:
 CONTACT RESISTANCE: 30m ohms MAX
 INSULATION RESISTANCE: 100M ohmsmin
 DIELECTIRC WITHSTANDING VOLTAGE:
 500V DC AT 1 MINUTE

TABLE NPAKT NUMBERING CODE:

U B X X X X - X X X X X
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
 UA:USB A TYPE
 UB:USB B TYPE
- ② P.C.B
 P1:DIP90°
 P2:DIP180°P3:SMT
- ③ 1: ONE LAYER
 2: TWO LAYER
 3: THREE LAYER
- ④ 1: RIGHT ANGLE
 2: FLCNK
- ⑤ 1: NO BACK SHELL
 2: HAVE BACK SHELL
- ⑥ N: NICKELT: TIN
 G: GOLD C:COVER
- ⑦ 1: 1u" 2: 3u" 3: 5u"
 4: 10u" 5: 15u" 6: 30u"
- ⑧ COLOR ⑨ NO:X X
 1: BLACK
 2: WHITE 3: BEIGE ...
- C1:SOLDER C2:CRIMP PIN
 C3:ASSEMBLAG C4:MOLDED

No.	PART NAME	DESCRIPTION	THICKNESS	Q'TY	SUPPLIER
1	HOUSING	PBT		1	B0001
2	CONTACT1	Phosphor Bronze	0.25mm	2	B0001
3	CONTACT2	Phosphor Bronze	0.25mm	2	B0001
4	BACK SHELL	STEEL	0.30m	1	B0001
5	FRONT SHELL	BRASS	0.30m	1	B0001

TOLERANCE				DWG NO: UF006		???????????		
SELECT			✓	DR:		TITLE: USB-B TYPE FEMALE 90° DIP TYPE		
DN	TOL	1	2	3	CHKD:	PART NO: UBP1--2-XXX06		
0.000 +/-	0.02	0.05	0.10		SALES:	CUSTOMER NAME:		
0.00 +/-	0.05	0.10	0.15		APPD:	CUSTOMER P/N:		
0.0 +/-	0.10	0.15	0.20			UNIT SCALE REV.		
0 +/-	0.15	0.20	1.00			MM NONE A1		
ANGLE+/-	1.0°	1.0°	1.5°					
MATERIAL:								