



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/28/2020	MBLACKWOOD



MODEL NO.	LENGTH(mm)	INCHES
VHA00021-0.5M	500±20	19.68 ±.79
VHA00021-01M	1000±30	39.37 ±1.18
VHA00021-02M	2000±30	78.74 ±1.18

- NOTES:**
- ELECTRICAL TEST:**
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CONTACT RESISTANCE: 5 OHM MAX
 INSULATION RESISTANCE: 5M OHM MIN
 HI-POT TEST: DC 300V/10ms
 PASS 8K@60Hz/48Gbps TEST
 - PACKAGING:**
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED INTO A CLEAR POLYBAG, LABEL PER LSP-010.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [5] ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS DRAWN BY: MVEERAPPAN CHECKED BY: DFRISIELLO APPROVED BY: MBLACKWOOD	DATE 09/28/2020 09/28/2020 09/28/2020	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY AUDIO/VIDEO
REF	SIZE A	CAGE CODE 43321	ITEM NO. VHA00021
SCALE: NONE	CAD FILE: VHA00021.SLDDRW	SHEET 1 OF 1	