



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/03/2020	MBLACKWOOD



PIN ASSIGNMENT



NOTES:

- ELECTRICAL TEST:**
 CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
 CONTACT RESISTANCE: 5 OHM MAX
 INSULATION RESISTANCE: 5M OHM MIN
 HI-POT TEST: DC 300V/10ms
 PASS 8K@60Hz/48Gbps TEST
- PACKAGING:**
 CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED INTO A CLEAR POLYBAG, LABEL PER LSP-010.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	APPROVALS DRAWN BY MVEERAPPAN CHECKED BY DFRISIELLO APPROVED BY MBLACKWOOD	DATE 09/28/2020 09/28/2020 09/28/2020	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR	CATEGORY AUDIO/VIDEO	PRODUCT DESCRIPTION ULTRA HIGH SPEED HDMI CABLE, M/M
THIRD-ANGLE PROJECTION 	SIZE A	CAGE CODE 43321	ITEM NO. VHA00021-3M