

UNCONTROLLED DOCUMENT

NOTES:

HOLE SIZE: .625

MAXIMUM PANEL THICKNESS: .125

MAXIMUM I.D. : .437

MATERIAL: HEAT STABILIZED NYLON UL 94V2

STOCKED IN STANDARD BLACK

TEMPERATURE INDEX: 105° C

WHITE AVAILABLE UPON REQUEST

$\phi .718 \pm .015$

$.062 \pm .015$

$.406 \pm .015$

TOLERANCES UNLESS NOTED

$\pm .005$ ON DIMENSIONS THRU .625

$\pm .008$ ON DIMENSIONS .626 THRU 1.000

$\pm .010$ ON DIMENSIONS 1.001 THRU 1.500

$\pm .015$ ON DIMENSIONS LARGER THAN 1.500

$\pm .015$ ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
ALL-FIT ADJUSTABLE BUSHING
MICRO P/N 22AF0625
DWG. # 22AF0625
FILE SERVER\ENG\WEB

MATERIAL: AS NOTED

DATE

SCALE
4:1

JDD