



RECOMMENDED PCB LAYOUT
TOP VIEW

N = Number of poles
Dim L = N x 5.08
Dim P = (N - 1) x 5.08

	Dim L	Dim P
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	02/09'06	Part No. is changed.	Marvin
△	06/23'06	Torque standard is changed from 3.5 Lb-In to 2.6 Lb-In	Marvin
△	06/23'06	Added cULus logo	Marvin
△	04/03'10	Part No. is changed.	Tason
△	10/25'13	Update the drawing	Guoxue
△	08/11'15	Update the drawing	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- △ Item ① Terminal body: Brass(CuZn), Bright Tin plated over Nickel plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Terminal housing: Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- △ ● Current rating: 16A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- △ ● Torque: 2.6Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval: cULus
- Critical dimension: ▽

TC xx 2 3 x x xxxx G △ △ △

POLES
02 02 POLES
03 03 POLES
...
24 24 POLES

△ Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Multiple colors

DIM C Length
0 4.4mm
1 3.8mm
2 3.5mm

0000:"@Logo (Standard)
000A:"ANYTEK"Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TC-5.08 Series 2-Interlock						
PART NO.	TCxx23xxxxxxG 				DWG NO.	8TC0603	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			