



DESCRIPTION							MOUNTING HOLE			BUSHINGS	
MICRO P/N	UL/CSA DESCRIPTION	CROSS SECTION	CABLE SIZE	CABLE TYPE	GAUGE (AWG)	STRAP TYPE	DIA. A	FLATS B	MAX PANEL TH C	LENGTH D	WIDTH E
23MP06N35	MP6N35	ROUND	0.390	SJO	18/2	Y	0.625	0.550	0.062	0.580	0.703
			(9,9)				(15,9)	(14,0)	(1,6)	(14,7)	(17,9)
			0.390	SJ	18/2						
			(9,9)								
			0.405	SJT	16/2						
			(10,3)								
23MP06N40	MP6N4	ROUND	0.405	SJO	18/2						
			(10,3)								
			0.390	SJT	18/2						
23MP06N44	MP6N44	FLAT	0.390								
			(9,9)								
23MP06N40	MP6N4	ROUND	0.300	SJT	18/2	Y	0.625	0.550	0.062	0.585	0.703
			(7,2)	SJO	18/2		(15,9)	(14,0)	(1,6)	(14,8)	(17,9)
23MP06N44	MP6N44	FLAT	0.120 X 0.300	SPT-1		Y	0.625	0.570	0.062	0.600	0.690
			(3,0 X 7,6)		18/3		(15,9)	(14,4)	(1,6)	(15,2)	(17,5)

TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625  
±.008 ON DIMENSIONS .626 THRU 1.000  
±.010 ON DIMENSIONS 1.001 THRU 1.500  
±.015 ON DIMENSIONS LARGER THAN 1.500  
±.015 ON FRACTIONAL DIMENSIONS

ENGINEERING APPROVED DRAWING  
RELEASE LEVEL    DATE

REV.	WAS	BY	DATE
A	.580[14,7]	TA	06/17/09

PRINT 10 OF 16  
PROPERTY OF  
**MICRO PLASTICS INC.**

CATALOG PRINT  
STRAIN RELIEF  
JOB N/A  
CUSTOMER P/N N/A  
MICRO P/N AS NOTED  
DWG 23MP\_ FILE SERVER\ENG

MATERIAL: HEAT STABILIZED NYLON  
BLACK

DATE 03/26/03	SCALE NONE	TA
------------------	---------------	----