



P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL ISSUE	19AUG2020	SM	MZ
	2	DRAFTING UPDATES	03SEP2020	SM	MZ
	A	PRODUCT UNDER TESTING	24NOV2020	SM	MZ

NOTES:

1. MATERIALS:
PLASTICS: PBT+PC ALLOY, UL-V0, UV-F1
CONTACTS: COPPER ALLOY, TIN PLATED
2. OPERATING RATINGS :
VOLTAGE (max): 600Vac Max
CURRENT (max): 25A ON 4.0mm² & 20A ON 12AWG
TEMPERATURE : -40°C TO 85°C
IP RATING : IP67 & IP68
3. FOR ASSEMBLY INSTRUCTIONS, REFER APPLICATION SPECIFICATION 114-133123
4. PACKAGING: MOQ 200 pcs IN PE BAG





SCALE 1:1




PRODUCT UNDER TESTING


CONTACT PRODUCT ENGINEERING BEFORE USING THIS PRINT



POLARIZING KEY A
2359420-1



POLARIZING KEY B
2359420-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M 19AUG2020	TE Connectivity			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK M. ZUCCA 03SEP2020	NAME NECTOR T, 3Pos, T-SPLITTER			
		APVD PETER OTT 24NOV2020				
	0 PLC ±0.4 1 PLC ±0.4 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±1°	PRODUCT SPEC 108-133123				
		APPLICATION SPEC 114-133123				
MATERIAL - -	FINISH - -	WEIGHT -				
CUSTOMER DRAWING			SCALE 3:2	SHEET 1	OF 1	REV A