




| PART NO.   | DIM. "A"<br>±.015 (0.4) | DIM. "B"<br>REF. | DIM. "C"<br>REF. |
|------------|-------------------------|------------------|------------------|
| SHK-6-01   | 3/8 (9.5)               | .54 (13.6)       | .77 (19.5)       |
| SHK-8-01   | 1/2 (12.7)              |                  |                  |
| SHK-12-01  | 3/4 (19.1)              |                  |                  |
| SHK-16-01  | 1 (25.4)                |                  |                  |
| SHK-20-01  | 1-1/4 (31.8)            | .81 (20.6)       | 1.14 (29.0)      |
| SHKE-6-01  | 3/8 (9.5)               |                  |                  |
| SHKE-8-01  | 1/2 (12.7)              |                  |                  |
| SHKE-12-01 | 3/4 (19.1)              |                  |                  |
| SHKE-16-01 | 1 (25.4)                |                  |                  |
| SHKE-20-01 | 1-1/4 (31.8)            |                  |                  |

NOTES:

- MAT'L: NYLON 66 (RMS-01).  
FLAME RETARDANT NYLON (RMS-19),  
AVAILABLE BY SPECIAL ORDER.
- COLOR: NATURAL.

|                                                                                |                  |              |      |           |  |            |  |
|--------------------------------------------------------------------------------|------------------|--------------|------|-----------|--|------------|--|
| TITLE: STAND-OFF HARNESS CLIP                                                  |                  |              |      |           |  | DWG IN     |  |
| TOLERANCES<br>UNLESS NOTED<br>.XX=±.010<br>.XXX=±.005<br>FRAC=±1/64<br>ANG=±1° | FILE # SHK(E)    | DWN: P.B.    | APP: | FINAL     |  |            |  |
| MAT'L: SEE NOTES                                                               | RE: RICHCO, INC. | DT: 05-12-94 | DT:  | PART #    |  | PRINT TYPE |  |
| RICHCO INC.<br>PO BOX 804238, CHICAGO, 60680<br>(773) 539-4060                 |                  |              |      | SEE TABLE |  | CA         |  |

|     |                          |             |
|-----|--------------------------|-------------|
| J   | SEE ECN #860 FOR CHANGES | SM 10.01.04 |
| REV | DESCRIPTION              | ENGR DATE   |