

Connector Location A

Connector Location B

Mating face acc. to IEC 61076-3-124

X



Y

HARTING ix Industrial Cat. 6A, 10-pole, type A IDC (IP20)

X
male

Loading Plan
acc. to TIA/EIA 568B

Y
male



Contacts 3 and 8 are not connected on both sides

- Contact material: copper alloy
- Contact area: Gold 0.2µm min.

Temperature range:

- Fixed installation: -20°C ... +60°C
- Dynamic installation: 0°C ... +50°C

NOTE:

For lengths < 1.0m:

- relative positioning of the connectors to each other will be as presented in the drawing, however with an admissible angular deviation around cable axis of ± 30°

For lengths ≥ 1.0m:

- relative positioning of the connectors to each other not obligatory

6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
Step	a [m]	XXX

Cat. 7 FRNC Ethernet Cable,
AWG 26/7, S/FTP, yellow

33480101826XXX

Type of cable

Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved		Created by BANCUID Banciu		Inspected by COSTEA Costea		Standardisation MUNTEANV Muntean	
Department HCS - RO		Title ix Industrial Cat.6A FRNC yellow		Date 2020-12-16		State Final Release	
HARTING Customised Solutions		Type TB		Number 33480101826XXX		Doc-Key / ECM-Nr. 100882410/UGD/000/C 500000186322	
D-32339 Espelkamp						Rev. C	
						Page 1/1	